
### **V-Band Balanced Mixer**

# **Description:**

**Model SFB-15-N1** is a V Band balanced mixer that utilizes high performance GaAs Schottky beam-lead diodes and a balanced circuit configuration to offer superior RF performance. The mixer supports the full waveguide band operation for both LO and RF frequencies from 50 to 75 GHz with an extremely broad IF output from DC to 25 GHz. The mixer offers a conversion loss of 9 dB typical and a high RF to LO port isolation of 30 dB.



### **Features:**

- Full Waveguide Band Coverage
- Low Conversion Loss
- High IF Frequency up to 25 GHz

# **Applications:**

- IEEE 802.11.ad WiGig Systems
- Radar Systems
- Communication Systems
- Test Equipment

# **Electrical Specifications:**

Parameter	Minimum	Typical	Maximum
RF Frequency	50 GHz		75 GHz
LO Frequency	50 GHz		75 GHz
IF Frequency	DC		25 GHz
LO Pumping Power	+10 dBm	+13 dBm	+15 dBm
Input P <sub>1dB</sub>		-3 dBm	
Conversion Loss		9 dB	12 dB
RF to LO Isolation		30 dB	
Combined RF and LO Power			+18 dBm
Specification Temperature		+25°C	
Case Temperature	-40°C		+85°C

# **Mechanical Specifications:**

Item	Specification		
RF	WR-15 Waveguide with UG-385/U Flange		
LO	WR-15 Waveguide with UG-385/U Flange	D. Pf	
IF	K(F)	719	
Case Material	Aluminum		
Finish	Gold Plated		
Weight	0.8 Oz		
Outline	FB-NV		




ESD


www.sagemillimeter.com | 3043 Kashiwa Street, Torrance, CA 90505 Phone: 424-757-0168 | Fax: 424-757-0188 | Email: sales@sagemillimeter.com

### V-Band Balanced Mixer

# **Typical Conversion Loss vs. Frequency**



# **Mechanical Outline:** (Unless otherwise specified, all dimensions are in inches)





ESD



#### Note:

- All data presented is collected from a sample lot. Actual data may vary unit to unit slightly.
- All testing was performed under +25 °C case temperature.
- SAGE Millimeter, Inc. reserves the right to change the information presented without notice.

#### Caution:

- Exceeding absolute maximum ratings shown will damage the device.
- The device is static sensitive. Always follow ESD rules when working with the device.
- The IF port of the mixer is DC coupled. Use a DC block when connecting to other devices. **Do not apply an external bias voltage to the IF port.**
- Any foreign objects in the waveguide will cause performance degradation and can possibly damage the device.
- Proper torque,  $8.0 \pm 0.15$  inch-pounds (0.92  $\pm$  0.05 Nm), should be applied. **SAGE Millimeter** torque wrench, model SCH-08008-S1, is highly recommended.





